

 **GRS 180**
by GETECHA

 **GRS 300**
by GETECHA

Better slanted, well-trieed thousand fold

Into the large intake and then into the tilted rotor. There every kind of granulate is reliably granulated. The GRS granulators run in peak operation right from the start.




- **Divided cutting chamber**
 - Easy screen removal
 - Cutting chamber opens without tools
 - Fast, economical cleaning

- **Nearly insatiable**
 - Large cutting chamber opening
 - Starts when the hopper is full

- **Self-cleaning steel plate**
 - Low fines
 - Wear-proof hardened
 - Easy to clean

- **Sophisticated safety engineering**
 - DIN EN 954-1, Cat. 3

- **By request and nevertheless standard**
 - Various rotor variants and wear-protection packages available
 - Hopper, frame or material container tailored to your production
 - Optional water cooling or filling level monitoring



	A	B	C
GRS 180	1.220 mm	665 mm	710 mm
GRS 300	1.600 mm	900 mm	930 mm

	A	B	C
GRS 180	1.660 mm	665 mm	710 mm
GRS 300	1.960 mm	900 mm	930 mm